

34610-OP 10W BROAD SPECTRUM "GROW" LED

REQUIRES: CURRENT LIMITING RESISTOR or LED DRIVER MOUNTING TO HEATSINK WITH THERMAL PAD

380-840nm High Brightness 10W "Grow Light" LED. Used for Home-gardening, Hydroponics, Horticulture, Greenhouse Vegetable & Flower cultivation Max forward current 1A continuous, 9-11VDC Forward voltage drop. 120deg. View angle. 5V max reverse Voltage. 20mm sq. X3.5mm SURFACE MOUNT PACKAGE 5mm X 6mm Beam leads **SQ:**20mm **H:** 3.5mm **WT:** .02





Information obtained from or supplied by Mpja.com or Marlin P. Jones and Associates inc. is supplied as a service to our customers and accuracy is not guaranteed nor is it definitive of any particular part or manufacturer. Use of information and suitability for any application is at users own discretion and user assumes all risk.



MARLIN P. JONES & ASSOC., INC.
P.O. Box 530400 Lake Park, FI 33403
800-652-6733 FAX 561-844-8764 WWW.MP.JA.COM